



CLEAN

SAFE

CERTIFIED

CLEANLINESS THROUGH ACCESSIBILITY

The patented mechanism allows the separate removal of seat and lid with just one hand. The hinge area can now be cleaned with appropriate cleaners. Seat and lid are cleaned with mild soapy water under the shower jet or optionally mechanically processed in an industrial dishwasher (plug-in dishwasher).

SAFETY THROUGH STABILITY

8 mm thick stainless steel hinge with full-length hinge axis for an extremely firm hold on the ceramic. Especially people with limited mobility (handicap, advanced age) appreciate this plus in safety.

The hinge is suitable for all common bathrooms. Simply remove the existing seat and attach the HYTO system hinge with the enclosed tool.

Rinse with clear water each time you clean and do not leave any cleaning residue on the hinge.

FUTURE-ORIENTED THROUGH CERTIFICATION

The basis for HYTO SAN is the „melamine“ material. This material resists the effects of damp heat during machine cleaning.

In medical tests, HYTO SAN toilet seats have proven to be the first sterilizable toilet system to use moist pressure and heat. This high material quality guarantees a consistent surface of quality and stability.



HYTO GmbH
Hochfeld 242
5721 Piesendorf
Austria

Tel.: +43 660 2370221
E-Mail: info@hyto.at
URL: www.hyto.at



**ORDER ONLINE
AT HYTO.AT**

OUR PRODUCTS

HYTO PLUS

Suitable for:
Household & normal use

Scope of delivery:

- Stainless steel hinge
- Seat + Lid

Material: UREA -
Cleaning under
running water



HYTO MED

12 cm booster seat

Practical hygiene gap on
the front side

Scope of delivery:

- Stainless steel hinge
- Seat + Clip

Material: PP -
suitable for
machine cleaning



HYTO SAN

Suitable for:
hospital, nursing homes,
accommodation facilities

Scope of delivery:

- Stainless steel hinge
- Seat + Lid

Material: Melamine -
suitable for
machine cleaning



HYTO PUR

made for heavily
frequented areas

Scope of delivery:


- Stainless steel hinge
- Seat + Clip

Material: PP / Melamine -
suitable for
machine cleaning



DIMENSIONS


HYTO PLUS / SAN




Opening angle: 115°.

Load capacity: up to 150 kg

Weight without hinge: approx. 2 kg



HYTO MED



HYTO SYSTEM

One hinge - 4 different variants for your individual solution!

Flexible due to HYTO MODULAR - more information at www.hyto.at